



ISOMETRIC VIEW

STRIDE INDUSTRIAL UNMANAGED, POE++ INJECTOR, IEEE 802.3AF/AT/BT, UP TO 90W, 2 PORTS, (1) POE++ GIGABIT (RJ45) AND (1) ETHERNET GIGABIT (RJ45) PORT(S), 9-55 VDC NOMINAL INPUT, -40 TO +75 DEG C, 35MM DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED.

SE3-IJ2B2UG-T

AutomationDirect.com
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 5/16/2024	SHEET 1 OF 1
--	--------------	-----------------	--	--------------------------------------	--	--------------	-----------------------------	--------------