



ISOMETRIC VIEW

* RJ45, FIBER PORT LED'S = ON-LINK, FLASH-DATA TRANSMITTING

STRIDE INDUSTRIAL UNMANAGED ETHERNET MEDIA CONVERTER, 2 PORTS, (1) ETHERNET 10/100BASE-T (RJ45) AND (1) MULTI-MODE SC 100FX FIBER PORT(S), (1) FORM A (SPST) RELAY, -40 TO +80 DEG C, METAL HOUSING, IP30, 35MM DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED.

SE3-MC2U-C1-T

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
5/16/2024

SHEET 1 OF 1