



\* RJ45, FIBER PORT LED'S = ON-LINK, FLASH-DATA TRANSMITTING

STRIDE INDUSTRIAL UNMANAGED ETHERNET MEDIA CONVERTER, 2 PORTS, (1) ETHERNET 10/100BASE-T (RJ45) AND (1) MULTI-MODE ST 100FX FIBER PORT(S), (1) FORM A (SPST) RELAY, -40 TO +80 DEG C, METAL HOUSING, IP30, 35MM DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED.

**SE3-MC2U-T1-T**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
5/16/2024

SHEET 1 OF 1