



ISOMETRIC VIEW

FIBER PORT: 1*100/1000 SFP SLOT
 DIP SWITCH 1: LINK-FAULT PASS THROUGH (LFP) ENABLE / DISABLE
 DIP SWITCH 2: 1000MBPS / 100MBPS

STRIDE INDUSTRIAL UNMANAGED ETHERNET MEDIA CONVERTER, 2 PORTS, (1) ETHERNET 10/100/1000BASE-T (RJ45) AND (1) SFP COMBO GIGABIT PORT(S), (1) FORM A (SPST) RELAY, -40 TO +80 DEG C, METAL HOUSING, IP30, 35MM DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED.

SE3-MC2UG-1P-T

AutomationDirect.com
 1-800-633-0405



3rd ANGLE

NOT TO SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED FOR PART DESIGN

UNLESS OTHERWISE SPECIFIED UNITS ARE:

mm [inch]

LATEST VERSION 5/16/2024

SHEET 1 OF 1