



ISOMETRIC VIEW



STRIDE INDUSTRIAL UNMANAGED POE++ SWITCH, IEEE 802.3AF/AT/BT, UP TO 240W, 5 PORTS, (4) POE++ 10/100/1000BASE-T (RJ45) AND (1) SFP COMBO GIGABIT PORT(S), 9-55 VDC NOMINAL INPUT, -40 TO +75 DEG C, 35MM DIN RAIL OR PANEL MOUNT, HAZARDOUS LOCATION RATED.

# SE3-SWP2B5UG-1P-T

AutomationDirect.com  
1-800-633-0405

	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	METRIC UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	mm [inch]	LATEST VERSION 5/16/2024	SHEET 1 OF 1
--	-----------	--------------	---	-----------------------------------	---------------------------------------	-----------	--------------------------	--------------