



2-WAY, 2-POSITION, GLASS-FILLED NYLON BODY, STACKABLE, 24 VAC/VDC OPERATING VOLTAGE, 7.2W, 18MM DIN STYLE WIRING PLUG. RA-3903 HIGH-FLOW TURBINE AND SF-9130 SCREEN INCLUDED.

CITO STACKVALVE MODULAR SOLENOID VALVE				SV-1024-30-H			AutomationDirect.com 1-800-633-0405	
	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	inch [mm]	LATEST VERSION 10/1/2024	SHEET 1 OF 1