



2-WAY, 2-POSITION, GLASS-FILLED NYLON BODY, STACKABLE, 120 VAC OPERATING VOLTAGE, 12VA, 18MM DIN STYLE WIRING PLUG. RA-3903 HIGH-FLOW TURBINE AND SF-9130 SCREEN INCLUDED.

<b>CITO STACKVALVE MODULAR SOLENOID VALVE</b>				<b>SV-1120-30-H</b>			AutomationDirect.com 1-800-633-0405	
	3rd ANGLE	NOT TO SCALE	PART DIMENSIONS MAY DIFFER SLIGHTLY DUE TO MANUFACTURER'S VARIANCES	INCH UNITS USED FOR PART DESIGN	UNLESS OTHERWISE SPECIFIED UNITS ARE:	<b>inch</b> <b>[mm]</b>	LATEST VERSION 9/18/2024	SHEET 1 OF 1