



EVER MOTION SOLUTIONS DC OPEN LOOP MICROSTEPPING STEPPER DRIVE, 4.2A PER PHASE, 2-PHASE OUTPUT, 12-48 VDC, BIPOLAR, VELOCITY AND POSITION MODE, 200 TO 65536 STEPS PER REVOLUTION, (2) ETHERNET 100BASE-TX (RJ45) AND (1) 4-PIN TERMINAL PORT(S)

**SW3D2042H241-01**

AutomationDirect.com  
1-800-633-0405



3rd  
ANGLE

NOT TO  
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY  
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED  
FOR PART DESIGN

UNLESS OTHERWISE  
SPECIFIED UNITS ARE:

mm  
[inch]

LATEST VERSION  
3/24/2025

SHEET 1 OF 1