



U.S. MOTORS ACCU-TORQ PREMIUM EFFICIENCY AC INDUCTION MOTOR, HIGH-PERFORMANCE INVERTER DUTY, 7-1/2HP, 3-PHASE, 230/460 VAC, 1800RPM, TENV, NEMA 213TC FRAME, ALUMINUM, C-FACE/RIGID BASE MOUNT, AVTRON HS35A ENCODER INCLUDED

UN7T2BC-HS35A

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

INCH UNITS USED FOR
PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

inch
[mm]

LATEST VERSION
8/27/2024

SHEET 1 OF 1