



OPEN CORE, 40 VA, 1-PHASE, 208/230/380/400/415/440/460/480/500/525/550/575/600
VAC PRIMARY, 12/24 VAC SECONDARY, 50/60 Hz, PANEL OR 35mm DIN RAIL MOUNT.

BLOCK CONTROL TRANSFORMER

USTE40_2X12

AutomationDirect.com
1-800-633-0405



3rd
ANGLE

NOT TO
SCALE

PART DIMENSIONS MAY DIFFER SLIGHTLY
DUE TO MANUFACTURER'S VARIANCES

METRIC UNITS USED
FOR PART DESIGN

UNLESS OTHERWISE
SPECIFIED UNITS ARE:

mm
[inch]

LATEST VERSION
10/31/2024

SHEET 1 OF 1