

# 22mm Metal Pilot Device Accessories

## Replacement Incandescent Bulbs

Replacement Incandescent Bulbs				
Part Number	Quantity	Price	Rating	Description
<a href="#">ECX1900-5</a>	5	\$9.50	6V@ 200mA , 1.2 watts	6V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4
<a href="#">ECX1902-5</a>	5	\$9.50	24V@ 80mA 2 watts	24V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4
<a href="#">ECX1904-5</a>	5	\$20.00	130V@20mA 2.6 watts	120V replacement bulb for 22mm switches and indicators. Miniature bayonet base T31/4

Note: Bulb removal tool available. Order part number HT8LAMPTOOL.



[ECX1902-5](#)

## Replacement LED Lamps

Replacement LED Lamps					
Part Number	Color	Quantity	Price	Rating	Description
<a href="#">ECX1911-2</a>	Red	2	\$17.50	24V@26mA 0.6 watts	LED replacement lamp for miniature bayonet bases Works with 22mm switches and indicators, but illumination will not be as even when used with the ECX 22mm indicators Note: Will not replace sealed Cutler-Hammer monoblock LED indicators.
<a href="#">ECX1912-2</a>	Green		\$22.00		
<a href="#">ECX1913-2</a>	Yellow		\$17.50		
<a href="#">ECX1914-2</a>	Blue		\$23.50		
<a href="#">ECX1915-2</a>	White		\$28.00		
<a href="#">ECX1921-2</a>	Red		\$17.50	120V@5mA 0.6 watts	
<a href="#">ECX1922-2</a>	Green		\$22.00		
<a href="#">ECX1923-2</a>	Yellow		\$17.50		
<a href="#">ECX1924-2</a>	Blue		\$23.50		
<a href="#">ECX1925-2</a>	White		\$28.00		



[ECX1915-2](#)

## Hole plug

Hole Plug			
Part Number	Color	Price	Description
<a href="#">ECX1490</a>	Black	\$2.75	Plastic hole plug for 22.5 mm openings in panels and enclosures; supplied with O-ring and mounting screw. Two plugs per package.



[ECX1490](#)

## Pilot Light Replacement Lens

Pilot Light Replacement Lens				
Part Number	Lamp Color	Price	Description	Use with
<a href="#">PL1170PR-5</a>	Red	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	Part numbers starting with GCX123
<a href="#">PL1170PV-5</a>	Green	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	
<a href="#">PL1170PG-5</a>	Yellow	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	
<a href="#">PL1170PB-5</a>	Blue	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	
<a href="#">PL1170PN-5</a>	Clear	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	
<a href="#">PL1170PW-5</a>	White	\$7.00	22mm metallic series pilot light replacement lens, 5/pk	



[PL1170PR-5](#)

# 22mm Metal Pilot Device Accessories

## Protective Covers for Pushbuttons

Protective Covers for Pushbuttons				
Part Number	Color	Quantity	Price	Description
<a href="#">ECX1700-5</a>	Black	5	\$7.50	Silicone protective covers for use with 22mm standard-size flush pushbuttons.  Will not work with Cutler-Hammer pushbuttons, 22mm plastic illuminated or extended pushbuttons, or 22mm plastic pushbuttons with 40mm actuator face.
<a href="#">ECX1701-5</a>	Red		\$7.50	
<a href="#">ECX1702-5</a>	Green		\$7.50	
<a href="#">ECX1703-5</a>	Yellow		\$7.50	
<a href="#">ECX1704-5</a>	Blue		\$7.50	
<a href="#">ECX1705-5</a>	Clear		\$7.50	
<a href="#">ECX1706-5</a>	Clear		\$13.00	Clear silicone protective covers for use with 2 mm illuminated and extended pushbuttons only. Will not work with Cutler-Hammer pushbuttons or 22mm mushroom pushbuttons.



[ECX1703-5](#)

## Replacement 22mm Support Base

Replacement 22mm Support Base				
Part Number	Quantity	Price	Drawing Link	Description
<a href="#">ECX1029-2</a>	1	\$7.00	<a href="#">PDF</a>	22mm metal support base Note: This item is supplied as a replacement part and is not required with any switch assembly. Will not work with Cutler-Hammer 22mm switches sold by AutomationDirect



[ECX1029-2](#)

## Replacement Contact Blocks

Replacement Contact Blocks					
Part Number	Quantity	Price	Drawing Link	Contacts	Description
<a href="#">ECX1030-2</a>	2	\$7.25	<a href="#">PDF</a>	Red, normally-closed (N.C.)	Replacement contact block for 22mm pushbuttons and selector switches.  Tightening Torque, terminal screw: 0.8Nm max mounting screw: 0.5Nm max Note: Will not work with Cutler-Hammer 22mm switches.
<a href="#">ECX1030-5</a>	5	\$17.00	<a href="#">PDF</a>		
<a href="#">ECX1040-2</a>	2	\$7.25	<a href="#">PDF</a>	Green, normally-open (N.O.)	
<a href="#">ECX1040-5</a>	5	\$17.00	<a href="#">PDF</a>		
<a href="#">ECX1042-2</a>	2	\$7.25	<a href="#">PDF</a>	Brown, normally-open (N.O.), push-push	



[ECX1030-2](#)

Note: See electrical specifications on [ECX Series 22mm Metal Pilot Devices Specifications](#) page at beginning of this section.

## Replacement Keys

Replacement Keys			
Part Number	Quantity	Price	Description
<a href="#">ECX1067-2</a>	Pkg of 2 sets (2 keys per set)	\$6.50	Replacement key for GCX series key-actuated selector switches, pack of 2 sets (2 keys each). NOTE: Will not work with Cutler-Hammer 22mm switches.



[ECX1067-2](#)

Note: All key-actuated 22mm metal selector switches are keyed alike.

# 22mm Metal Pilot Device Accessories

## EMERGENCY STOP Legend Plate

EMERGENCY STOP Legend Plate				
Part Number	Quantity	Price	Drawing Link	Description
<a href="#">ECX1651</a>	1	\$2.75	PDF	Oversize yellow circular EMERGENCY STOP legend plate for 22mm E-stop type mushroom pushbuttons, 60mm outside diameter.



[ECX1651](#)

## Knockout Punches

Ruko's knockout punch hole-cutting tool includes punch, die and draw bolt (without ball bearing). Use for sheet steel, stainless-steel sheets, non-ferrous and light metals, and plastics up to 0.16" (8 ga.) thick.

Replacement bolts are offered in three of the most popular sizes.

Note: Part number [109225](#) is recommended when punching holes for 22mm pilot devices.



[109225](#)

## Two-Position Short Lever Operator

2-Position Short Lever Replacement Operator				
Part Number	Lamp Color	Price	2-Position	Use with
<a href="#">GR1172PR-5</a>	Red	\$16.50	22mm 2-position selector switch illuminated short lever replacement operator, 5/pk	Part numbers starting with GCX124, GCX125 GCX324, GCX325
<a href="#">GR1172PV-5</a>	Green	\$16.50	22mm 2-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1172PG-5</a>	Yellow	\$16.50	22mm 2-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1172PB-5</a>	Blue	\$16.50	22mm 2-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1172PN-5</a>	Clear	\$16.50	22mm 2-position selector switch illuminated short lever replacement operator, 5/pk	



[GR1172PR-5](#)

## Three-Position Short Lever Operator

3-Position Short Lever Replacement Operator				
Part Number	Lamp Color	Price	3-Position	Use with
<a href="#">GR1288PR-5</a>	Red	\$16.50	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	Part numbers starting with GCX126, GCX128 GCX326, GCX328
<a href="#">GR1288PV-5</a>	Green	\$16.50	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1288PG-5</a>	Yellow	\$16.50	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1288PB-5</a>	Blue	\$16.50	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	
<a href="#">GR1288PN-5</a>	Clear	\$16.50	22mm 3-position selector switch illuminated short lever replacement operator, 5/pk	



[GR1288PR-5](#)

# 22mm Metal Pilot Device Accessories

## Mushroom Switch Replacement Operator

Mushroom Switch Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
<a href="#"><u>PL1171PR-5</u></a>	Red	\$7.25	22mm, illuminated momentary Mushroom switch replacement operator, red, 5/pk	Part numbers starting with GCX1221, GCX3221 mushroom-style illuminated pushbuttons
<a href="#"><u>PL1298P-5</u></a>	Red	\$7.25	22mm illuminated twist-to-release mushroom switch replacement operator, red, 5/pk	Part numbers starting with GCX1226, GCX3226 mushroom-style illuminated pushbuttons



[PL1298P-5](#)

## Flush Pushbutton Replacement Operator

Flush Pushbutton Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
<a href="#"><u>GR1168PR-5</u></a>	Red	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	Part numbers starting with GCX119, GCX120 GCX319, GCX320
<a href="#"><u>GR1168PV-5</u></a>	Green	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	
<a href="#"><u>GR1168PG-5</u></a>	Yellow	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	
<a href="#"><u>GR1168PB-5</u></a>	Blue	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	
<a href="#"><u>GR1168PN-5</u></a>	Clear	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	
<a href="#"><u>GR1168PW-5</u></a>	White	\$9.00	22mm illuminated flush pushbutton replacement operator, 5/pk	



[GR1168PR-5](#)

## Extended Pushbutton Replacement Operator

Extended Pushbutton Replacement Operator				
Part Number	Lamp Color	Price	Description	Use with
<a href="#"><u>PL1308PR-5</u></a>	Red	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	Part numbers starting with GCX121, GCX321
<a href="#"><u>PL1308PV-5</u></a>	Green	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	
<a href="#"><u>PL1308PG-5</u></a>	Yellow	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	
<a href="#"><u>PL1308PB-5</u></a>	Blue	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	
<a href="#"><u>PL1308PN-5</u></a>	Clear	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	
<a href="#"><u>PL1308PW-5</u></a>	White	\$7.00	22mm illuminated extended pushbutton, replacement operator, 5/pk	



[PL1308PR-5](#)

# 22mm Metal Pilot Device Accessories

## Legend Plates

Aluminum legend plates for use with 22mm pilot devices. Black or red field with silver background. O-ring included.



**ECX1670A-B04**



**ECX1670A-R03**

Aluminum Legend Plates						
Legend	Color of Field	Text Color	Background Color	Part Number	Price	Drawing Link
<b>AUTO OFF HAND</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B46</b></a>	\$3.75	<a href="#">PDF</a>
<b>Blank Plate</b>	Black	-	Silver	<a href="#"><b>ECX1670A-B</b></a>	\$3.75	<a href="#">PDF</a>
<b>Blank Plate</b>	Red	-	Silver	<a href="#"><b>ECX1670A-R</b></a>	\$3.75	<a href="#">PDF</a>
<b>CLAMP</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B24</b></a>	\$3.75	<a href="#">PDF</a>
<b>CLOSE</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B01</b></a>	\$3.75	<a href="#">PDF</a>
<b>DOWN</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B02</b></a>	\$3.75	<a href="#">PDF</a>
<b>EMERG. STOP</b>	Red	Red	Silver	<a href="#"><b>ECX1670A-R03</b></a>	\$3.75	<a href="#">PDF</a>
<b>EXTEND</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B51</b></a>	\$3.75	<a href="#">PDF</a>
<b>FEEDER OFF</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B26</b></a>	\$3.75	<a href="#">PDF</a>
<b>FEEDER ON</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B25</b></a>	\$3.75	<a href="#">PDF</a>
<b>FOR OFF REV</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B19</b></a>	\$3.75	<a href="#">PDF</a>
<b>FOR REV</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B13</b></a>	\$3.75	<a href="#">PDF</a>
<b>FORWARD</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B04</b></a>	\$3.75	<a href="#">PDF</a>
<b>GRIP</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B53</b></a>	\$3.75	<a href="#">PDF</a>
<b>HAND-AUTO</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B14</b></a>	\$3.75	<a href="#">PDF</a>
<b>HAND OFF AUTO</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B20</b></a>	\$3.75	<a href="#">PDF</a>
<b>HIGH</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B27</b></a>	\$3.75	<a href="#">PDF</a>
<b>HIGH LOW</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B43</b></a>	\$3.75	<a href="#">PDF</a>
<b>IN</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B28</b></a>	\$3.75	<a href="#">PDF</a>
<b>INCH</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B29</b></a>	\$3.75	<a href="#">PDF</a>
<b>JOG</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B05</b></a>	\$3.75	<a href="#">PDF</a>
<b>JOG FOR</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B30</b></a>	\$3.75	<a href="#">PDF</a>
<b>JOG REV</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B31</b></a>	\$3.75	<a href="#">PDF</a>
<b>JOG RUN</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B15</b></a>	\$3.75	<a href="#">PDF</a>
<b>LOW</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B32</b></a>	\$3.75	<a href="#">PDF</a>
<b>LOWER</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B33</b></a>	\$3.75	<a href="#">PDF</a>
<b>MAN AUTO</b>	Black	Black	Silver	<a href="#"><b>ECX1670A-B44</b></a>	\$3.75	<a href="#">PDF</a>

Note: Legend plate text is 3mm in height  
Continued on next page

# 22mm Metal Pilot Device Accessories

**ECX1670A-B48****ECX1670A-R11**

Aluminum Legend Plates (continued)						
Legend	Color of Field	Text Color	Background Color	Part Number	Price	Drawing Link
<b>MAN OFF AUTO</b>	Black	Black	Silver	<a href="#">ECX1670A-B47</a>	\$3.75	<a href="#">PDF</a>
<b>MOTOR RUN</b>	Black	Black	Silver	<a href="#">ECX1670A-B22</a>	\$3.75	<a href="#">PDF</a>
<b>MOTOR STOP</b>	Black	Black	Silver	<a href="#">ECX1670A-B23</a>	\$3.75	<a href="#">PDF</a>
<b>OFF</b>	Black	Black	Silver	<a href="#">ECX1670A-B34</a>	\$3.75	<a href="#">PDF</a>
<b>OFF ON</b>	Black	Black	Silver	<a href="#">ECX1670A-B16</a>	\$3.75	<a href="#">PDF</a>
<b>ON</b>	Black	Black	Silver	<a href="#">ECX1670A-B06</a>	\$3.75	<a href="#">PDF</a>
<b>OPEN</b>	Black	Black	Silver	<a href="#">ECX1670A-B07</a>	\$3.75	<a href="#">PDF</a>
<b>OPEN OFF CLOSE</b>	Black	Black	Silver	<a href="#">ECX1670A-B48</a>	\$3.75	<a href="#">PDF</a>
<b>OPEN CLOSE</b>	Black	Black	Silver	<a href="#">ECX1670A-B17</a>	\$3.75	<a href="#">PDF</a>
<b>OUT</b>	Black	Black	Silver	<a href="#">ECX1670A-B35</a>	\$3.75	<a href="#">PDF</a>
<b>POWER ON</b>	Black	Black	Silver	<a href="#">ECX1670A-B21</a>	\$3.75	<a href="#">PDF</a>
<b>PULL ON PUSH OFF</b>	Black	Black	Silver	<a href="#">ECX1670A-B50</a>	\$3.75	<a href="#">PDF</a>
<b>RAISE</b>	Black	Black	Silver	<a href="#">ECX1670A-B36</a>	\$3.75	<a href="#">PDF</a>
<b>READY</b>	Black	Black	Silver	<a href="#">ECX1670A-B37</a>	\$3.75	<a href="#">PDF</a>
<b>RELEASE</b>	Black	Black	Silver	<a href="#">ECX1670A-B54</a>	\$3.75	<a href="#">PDF</a>
<b>RESET</b>	Black	Black	Silver	<a href="#">ECX1670A-B38</a>	\$3.75	<a href="#">PDF</a>
<b>RETRACT</b>	Black	Black	Silver	<a href="#">ECX1670A-B52</a>	\$3.75	<a href="#">PDF</a>
<b>REVERSE</b>	Black	Black	Silver	<a href="#">ECX1670A-B08</a>	\$3.75	<a href="#">PDF</a>
<b>RUN</b>	Black	Black	Silver	<a href="#">ECX1670A-B09</a>	\$3.75	<a href="#">PDF</a>
<b>SAFE RUN</b>	Black	Black	Silver	<a href="#">ECX1670A-B45</a>	\$3.75	<a href="#">PDF</a>
<b>START</b>	Black	Black	Silver	<a href="#">ECX1670A-B10</a>	\$3.75	<a href="#">PDF</a>
<b>STOP</b>	Black	Black	Silver	<a href="#">ECX1670A-B11</a>	\$3.75	<a href="#">PDF</a>
<b>STOP</b>	Red	Red	Silver	<a href="#">ECX1670A-R11</a>	\$3.75	<a href="#">PDF</a>
<b>TEST</b>	Black	Black	Silver	<a href="#">ECX1670A-B39</a>	\$3.75	<a href="#">PDF</a>
<b>TRANSFER</b>	Black	Black	Silver	<a href="#">ECX1670A-B40</a>	\$3.75	<a href="#">PDF</a>
<b>TRIP</b>	Black	Black	Silver	<a href="#">ECX1670A-B41</a>	\$3.75	<a href="#">PDF</a>
<b>UNCLAMP</b>	Black	Black	Silver	<a href="#">ECX1670A-B42</a>	\$3.75	<a href="#">PDF</a>
<b>UP</b>	Black	Black	Silver	<a href="#">ECX1670A-B12</a>	\$3.75	<a href="#">PDF</a>
<b>UP OFF DOWN</b>	Black	Black	Silver	<a href="#">ECX1670A-B49</a>	\$3.75	<a href="#">PDF</a>
<b>UP DOWN</b>	Black	Black	Silver	<a href="#">ECX1670A-B18</a>	\$3.75	<a href="#">PDF</a>

Note: Legend plate text is 3mm in height

# 22mm Metal Pilot Device Accessories



**ECX1680A-B17**



**ECX1680A-R03**

Jumbo Aluminum Legend Plates						
Legend	Color of Field	Text Color	Background Color	Part Number	Price	Drawing Link
Blank Plate	Black	-	Silver	<a href="#"><u>ECX1680A-B</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
Blank Plate	Red	-	Silver	<a href="#"><u>ECX1680A-R</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>EMERG. STOP</b>	Red	Red	Silver	<a href="#"><u>ECX1680A-R03</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>HAND OFF AUTO</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B20</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>JOG</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B05</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>OFF ON</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B16</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>OPEN CLOSE</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B17</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>POWER ON</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B21</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>START</b>	Black	Black	Silver	<a href="#"><u>ECX1680A-B10</u></a>	\$4.25	<a href="#"><u>PDF</u></a>
<b>STOP</b>	Red	Red	Silver	<a href="#"><u>ECX1680A-R11</u></a>	\$4.25	<a href="#"><u>PDF</u></a>

Note: Legend plate text is 3mm in height

# E22 Series Cross-reference Tables

<b>Pushbutton, Indicator Light, and Selector Switch Cross Reference</b>				
<b>Cutler-Hammer</b>	<b>Allen-Bradley</b>	<b>Telemecanique XB2B (chrome bezel) XA2B (black bezel)</b>	<b>GE C-2000</b>	<b>Siemens</b>
<b>Non-Illuminated Pushbuttons</b>				
<a href="#">E22PB1A</a>	800EPF2 800E3LX10	ZA2BA2 ZA2BZ101	P9XPNG10N0	3SB1000-0AB01 3SB02-CBH 3SB1400-0B
<a href="#">E22PB3A</a>	800EPF3 800E3LX10	ZA2BA3 ZA2BZ101	P9XPVNG10N0	3SB1000-0AE01 3SB02-CBH 3SB1400-0B
<a href="#">E22EB2B</a>	800EPE4 800E3LX01	ZA2BL4 ZA2BZ102	P9XPNRS20N0	3SB1000-0LC01 3SB02-CBH 3SB1400-0B
<a href="#">E22ASB204</a>	ENCLSR: 800E-2P 800EP-F3 800E-2LX10 800EP-E4 800E-2LX01 800E-34BE208 800E-34R212	XALB211 Both flush - stop is not extended	P9CPNRSN20N0 P9CPNVGN10NO P9EPB02 P9AEPN201 P9AEPN202	3SB02-S21
<b>Illuminated Pushbuttons</b>				
<a href="#">E22TB2X4B</a>	800EPL4 800E3DL3 800E3X01	ZA2BW14 ZA2BW06224	P9XPLRSDN12NADI	3SB1001-0LC01 3SB02-CBH 3SB1400-0C 3SB1400-2H
<a href="#">E22TB3X4A</a>	800EPL3 800E3DL3 800E3X10	ZA2B213 AZ2B206124	P9XPLVSDN12NADI	3SB1001-0LE01 3SB02-CBH 3SB1400-0B 3SB1440-2H
<a href="#">E22TB9X4A</a>	800EPL5 800E3DL3 800E3X10	ZA2BW15 ZA2BW06124	P9XPLASDN12NADI	3SB1001-0LD01 3SB02-CBH 3SB1400-0B 3SB1400-2H
<a href="#">E22TB2X10B</a>	800EPL4 800E2RL5 800E3X01	ZA2BW14 ZA2BW062120	P9XPLRSB P9PRNVJ P9PDNVD	3SB1001-0LC01 3SB02-CBH 3SB1400-0C
<a href="#">E22TB3X10A</a>	800EPL3 800E2RL5 800E3X10	ZA2BW13 ZA2BW061120	P9XPLVSD P9PRNVJ P9PDNVD	3SB02-UPR1P 3SB1910-0DE 3SB1400-0B
<a href="#">E22TB9X10A</a>	800DPL5 800E2RL5 800E3X10	ZA2BW15 ZA2B2061120	P9XPLASD P9PRNVJ P9PDNVD	3SB02-UPR1P 3SB1910-0DD 3SB1400-0B



# GCX Series 22mm Plastic Pilot Devices Specifications


## Assembly information

These pushbuttons and indicator lights are supplied with the appropriate contact blocks, unless otherwise indicated. Use these drawings as a guide to make sure there is adequate clearance behind the panel.


## Dimensions

mm  
[inches]


**Pushbuttons and selector switches**




**Illuminated pushbuttons and selector switches/ indicator lights**



## Mounting



**This layout is suitable if all switches are 230V or less and the same polarity.**




**This layout is suitable if all switches are 400V or less and different polarity.**

**NOTE: Contact blocks can be arranged up to three deep by two wide.**



Typical Wiring



## Specifications

These specifications apply to all the GCX and ECX 22mm plastic pushbuttons and switches.

Physical Specifications		Electrical Specifications	
<b>Standards Reference</b>	CEI EN 60947-5-1, CSA C22-2 n.14	<b>Rated Thermal Current (contact block)</b>	A300, Q300 (Refer to E22 Series mounting/contact rating section for details)
<b>Approvals</b>	UL File E189258, IMQ (where specified)	<b>Rated Insulation Voltage</b>	Ui 660V according to CEI EN 60947-5-1, 300V according to CSA C22-2 n.14 and UL 508
<b>Enclosure Material</b>	Fiberglass reinforced thermoplastic	<b>Dielectric Strength</b>	3kV (1 second)
<b>Contacts Material</b>	Silver	<b>Insulation Resistance</b>	2MΩ min. (500VDC)
<b>Protection Degree</b>	IP40 for GCX3151-24, GCX3151-120, GCX3153-24 and GCX3153-120. IP65 for all others. (See Appendix of this catalog for explanation of IP ratings according to IEC 144 CEI 70-1.)	<b>Initial Contact Resistance</b>	≤ 25mΩ
<b>Electric Shock Protection</b>	IEC 536, Class II	<b>Short-Circuit Protection*</b>	Cartridge fuses gl 10 A-500V 10, 3x381 100 KA
<b>Temperature Ratings</b>	Storage: -40 to 80°C (-40 to 176° F) Operating: -25° to +70°C (-13° to 158° F)	<b>Terminal Markings</b>	According to CENELEC EN 50013
<b>Working Positions</b>	All working positions are allowed	<b>Connections</b>	Single screw with non-loosening plate clamp, 14AWG max., Tighten to 0.8Nm max
<b>Mechanical Life</b>	Pushbuttons, selector switches, joy stick switches: 1,000,000 operations Emergency mushrooms and push-push pushbuttons: 300,000 operations	<b>Contacts Operation</b>	Self-cleaning types EN01 (N.C.) EN 10 (N.O.) slow-action, positive opening
<b>Positive Opening Operation</b>	(according to IEC 947-5-1) All functions incorporating an NC contact are positive opening operation	<b>Operation Frequency</b>	3600 operations per hour max.
		<b>Utilization Category</b>	AC15 (Control of AC electromagnetic loads) 24 volts AC at 10 amps 130 volts AC at 6.5 amps DC13 (Control of DC electromagnetic loads) 24 volts DC at 1.5 amps 110 volts DC at 0.5 amps

\*Note: Recommended, not supplied