

011900-00 Cut Sheet



Stego electronic thermostat, adjustable, 0 to 60 deg C, 3K switching differential, 24 VDC operating voltage, 35mm DIN rail mount, for electrical enclosure climate control.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/011900-00>

Technical Specifications

| | |
|-----------------------------------|--|
| Brand | Stego |
| Item | Electronic thermostat |
| IP Rating | IP20 |
| Setpoint Type | Adjustable |
| Contact 1 | 0 to 60 deg C |
| Switching Differential | 3K |
| Switching Tolerance | +/-1K |
| Operating Voltage | 24 VDC |
| Maximum Switching Capacity | 16A |
| Connection | 5-pole terminal for 14 AWG max solid or 16 AWG max stranded wire |
| Mounting | 35mm DIN rail |
| Application | For electrical enclosure climate control |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/011900-00.pdf>
See store item page for other formats.