

# 014202-00 Cut Sheet



Stego Smart Sensor temperature/humidity sensor, -40 to 140 deg F, 0 to 100% RH, 4-20 mA output, 35mm DIN rail or panel mount, 4-pin M12 quick-disconnect.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/014202-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Temperature/humidity sensor
<b>Series</b>	Smart Sensor
<b>Temperature Sensing Range</b>	-40 to 140 deg F
<b>Humidity Sensing Range</b>	0 to 100% RH
<b>Output</b>	4-20 mA
<b>Output 2</b>	4-20 mA
<b>Operating Temperature</b>	-40 to +158 deg F

<b>Operating Voltage</b>	24 VDC
<b>Body Material</b>	Plastic
<b>IP Rating</b>	IP20
<b>Mounting</b>	35mm DIN rail or panel
<b>Orientation</b>	Vertical
<b>Connection</b>	4-pin M12 quick-disconnect
<b>Additional Information</b>	Purchase cable separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E500143
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/014202-00.pdf>  
See store item page for other formats.