

018600-04 Cut Sheet



Stego exhaust fan, top mount, 203 CFM, 24 VDC operating voltage, G3 (coarse) filter mat, NEMA 3R, indoor use only, 9.69 x 9.69in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018600-04>

Technical Specifications

Brand	Stego
Airflow Direction	Exhaust
Item	Fan
Mounting	Top
With Air Flaps	No
Filter Media	G3 (coarse) filter mat
Free Airflow	203 CFM
Operating Voltage	24 VDC
Power Consumption	20W

Electrical Connection	2-pole clamp for AWG 14 wire, 7.1 in-lb maximum clamping torque
NEMA Rating	3R
Application	Indoor use only
IP Rating	IP32
Enclosure Cutout	9.69 x 9.69in
Color	RAL 7035 light gray
Includes	Mounting hardware
Additional Information	Purchase intake grille separately

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/018600-04.pdf>
See store item page for other formats.