

# 018802-00 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 18 CFM, 24 VDC operating voltage, with air flaps, NEMA 12, indoor use only, 3.62 x 3.62in enclosure cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018802-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Series</b>	Filter Fan Plus FPO
<b>Airflow Direction</b>	Exhaust
<b>Item</b>	Fan
<b>Mounting</b>	Side
<b>With Air Flaps</b>	Yes
<b>Free Airflow</b>	18 CFM
<b>Airflow with Grill and Filter(s)</b>	10 CFM
<b>Operating Voltage</b>	24 VDC
<b>Power Consumption</b>	2.7W
<b>Current Draw</b>	113 mA

<b>Electrical Connection</b>	(2) AWG 22 x 11.8in long wires
<b>Maximum Static Pressure</b>	37Pa
<b>Operating Temperature</b>	-4 to 158 deg F
<b>Average Noise Level</b>	48 dBA
<b>NEMA Rating</b>	12
<b>Application</b>	Indoor use only
<b>IP Rating</b>	IP54
<b>Enclosure Cutout</b>	3.62 x 3.62in
<b>Color</b>	RAL 7035 light gray
<b>Includes</b>	Optional mounting screws
<b>Additional Information</b>	Purchase intake grille separately

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/018802-00.pdf>  
See store item page for other formats.