


018809-40 Cut Sheet



Stego Filter Fan Plus FPO exhaust fan, side mount, 14 CFM, 115 VAC operating voltage, G3 (coarse) filter mat, NEMA 12, indoor use only, 3.62 x 3.62in cutout, RAL 7035 light gray.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/018809-40>

Technical Specifications

Brand	Stego	Current Draw	96 mA
Series	Filter Fan Plus FPO	Electrical Connection	(2) AWG 22 x 11.8in long wires
Airflow Direction	Exhaust	Maximum Static Pressure	56Pa
Item	Fan	Operating Temperature	-4 to 158 deg F
Mounting	Side	Average Noise Level	36 dBA
With Air Flaps	No	NEMA Rating	12
Filter Media	G3 (coarse) filter mat	Application	Indoor use only
Free Airflow	14 CFM	IP Rating	IP54
Airflow with Grill and Filter(s)	9.4 CFM	Enclosure Cutout	3.62 x 3.62in
Operating Voltage	115 VAC	Color	RAL 7035 light gray
Frequency	60 Hz	Includes	Optional mounting screws
Power Consumption	11W	Additional Information	Purchase intake grille separately. Fan will also safely operate at 50Hz, but with reduced airflow. Contact manufacturer for 50Hz performance data

Agency Approvals

UL Listed File #	None
UL Recognized File #	E234324
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document
Other	None