

# 030921-17 Cut Sheet



Stego enclosure heater, axial fan, 200W heating capacity, high performance cartridge heating element, 24 VDC operating voltage, adjustable thermostat with external sensor connection, N.C. (open on rise) -4 to 104 deg F, foot mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/030921-17>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>IP Rating</b>	IP20
<b>Fan Type</b>	Axial
<b>Heating Capacity</b>	200W
<b>Heating Element</b>	High performance cartridge
<b>Operating Voltage</b>	24 VDC
<b>Heater Control</b>	Adjustable thermostat with external sensor connection
<b>Contact 1</b>	N.C. (open on rise) -4 to 104 deg F
<b>Switching Differential</b>	5.4 deg F
<b>Switching Tolerance</b>	+/-1.8 deg F
<b>Mounting</b>	Foot
<b>Requires</b>	External temperature sensor

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E234324
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>