


# 060400-00 Cut Sheet



Stego enclosure heater, 10W heating capacity, touch-safe PTC resistor heating element, 120-240 VAC/VDC operating voltage, 35mm DIN rail mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/060400-00>

## Technical Specifications

<b>Brand</b>	Stego
<b>Item</b>	Enclosure heater
<b>IP Rating</b>	IP20
<b>Heating Capacity</b>	10W
<b>Heating Element</b>	Touch-safe PTC resistor
<b>Operating Voltage</b>	120-240 VAC/VDC
<b>Connection</b>	4-pole terminal for 14 AWG max solid or stranded wire
<b>Mounting</b>	35mm DIN rail

## Agency Approvals

<b>UL Listed File #</b>	None
<b>UL Recognized File #</b>	E150057
<b>UL Hazardous File #</b>	None
<b>CE</b>	<a href="#">View CE declarations</a>
<b>CSA File #</b>	None
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>