

10.02.01.01597 Cut Sheet



Schmalz basic vacuum ejector, 500.0 l/min (17.7 cfm) suction rate, G3/8 female BSPP inlet(s), G3/4 female BSPP vacuum port.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10.02.01.01597>

Technical Specifications

Brand	Schmalz
Item	Vacuum ejector
Ejector Type	Basic
Degree of Evacuation	60%
Suction Rate	500.0 l/min (17.7 cfm)
Air Consumption	160.0 l/min (5.7 cfm)
Average Noise Level	65 dbA
Inlet Port	G3/8 female BSPP
Vacuum Port	G3/4 female BSPP
Air Saving	No
Includes	Mounting hardware
Alternate ID	SBPL-50-HF

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/10.02.01.01597.pdf>
See store item page for other formats.