

10.02.02.04116 Cut Sheet



Schmalz compact vacuum ejector, 65.5 l/min (2.3 cfm) suction rate, G1/8 female BSPP inlet(s), G1/8 female BSPP vacuum port, air saving.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/10.02.02.04116>

Technical Specifications

Brand	Schmalz
Item	Vacuum ejector
Ejector Type	Compact
Degree of Evacuation	85%
Suction Rate	65.5 l/min (2.3 cfm)
Air Consumption	98.0 l/min (3.5 cfm)
Average Noise Level	73 dbA
Inlet Port	G1/8 female BSPP
Vacuum Port	G1/8 female BSPP
Air Saving	Yes
Valve Configuration	N.C.
Electrical Connection	5-pin M12 quick-disconnect
Switching Output	PNP
Alternate ID	SCPS-15-G02-NC-M12-50-PNP

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	No
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/10.02.02.04116.pdf>
See store item page for other formats.