

1120250200XP Cut Sheet



Metal Work pneumatic cylinder, ISO 6432 non-repairable, 25mm bore, 10mm rod diameter, 200mm stroke, double acting, magnetic piston, universal mount.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1120250200XP>

Technical Specifications

| | |
|----------------------|-------------------------|
| Brand | Metal Work |
| Item | Cylinder |
| Working Fluid | Air or inert gas |
| Cylinder Type | ISO 6432 non-repairable |
| Bore Diameter | 25mm |
| Stroke | 200mm |
| Port Size | G1/8 female BSPP |
| Mounting | Universal |

| | |
|-------------------------|-----------------|
| Action Type | Double acting |
| Magnetic Piston | Magnetic piston |
| Body Material | Stainless steel |
| End Cap Material | Aluminum |
| Rod Material | Stainless steel |
| Rod Diameter | 10mm |
| Rod Thread Size | M10x1.25 |
| Bushing Type | Bronze bushings |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/1120250200XP.pdf>
See store item page for other formats.