

122340-00 Cut Sheet



Stego Varioline LED enclosure light, 120 VAC operating voltage, no switch, 27.3in length, 1730 Lm, integral receptacle, screw mount, 3-pole plug with snap lock, 16W, IP20.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/122340-00>

Technical Specifications

| | |
|----------------------------|----------------------------|
| Brand | Stego |
| Item | LED enclosure light |
| Series | Varioline |
| Operating Voltage | 120 VAC |
| Switch Type | None |
| Length | 27.3in |
| Luminous Flux | 1730 Lm |
| Integral Receptacle | Yes |
| Mounting | Screw |
| Connection | 3-pole plug with snap lock |
| Power Consumption | 16W |
| IP Rating | IP20 |
| Requires | Power or extension cable |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | None |
| UL Recognized File # | E234324 |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | None |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/122340-00.pdf>
See store item page for other formats.