

13383144255 Cut Sheet



Pfannenberg DTS 3021 air conditioner, 1200 BTU/H, R-134a, 115 VAC operating voltage, carbon steel housing, RAL 7035 light gray, filter-free, side mount. For use with NEMA/UL Type 12 enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/13383144255>

Technical Specifications

Brand	Pfannenberg
Series	DTS 3021
Item	Air conditioner
Nominal Cooling Capacity	1200 BTU/H
Operating Voltage	115 VAC
Frequency	60 Hz
Running Current	3.3A
Refrigerant	R-134a
Height	15.43in
Width	7.1in
Depth	7.53in

Mounting	Side
Filter-Free	Yes
Housing Material	Carbon steel
Color	RAL 7035 light gray
IP Rating	IP54
For Use With	NEMA/UL Type 12 enclosures
Includes	Seal, mounting template, and hardware
Dangerous Goods	<ul style="list-style-type: none">• Packaging Instructions: 200• UN Number: 3159• Hazard Type: Compressed Gas

Agency Approvals

UL Listed File #	SA10300
UL Recognized File #	SA10300
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/13383144255.pdf>
See store item page for other formats.