

1414N4ALM6 Cut Sheet



Hammond enclosure, NEMA 4/4X/12/13, 14 x 12 x 6in (HxWxD), wall mount, 5052-H32 aluminum, lift-off cover, aluminum clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1414N4ALM6>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
3-Piece Assembly	No
Vented	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	14 x 12 x 6in (HxWxD)
Enclosure Height	14.31in
Enclosure Width	12.31in
Enclosure Depth	6.21in
Mounting	Wall

Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Bottom Gland Plate	No
Material	5052-H32 aluminum
Cover Type	Lift-off cover
Latch Type	Aluminum clamps
Number Of Latches	8
Shelf	No
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1414N4ALM6.pdf>
See store item page for other formats.