

1414N4ALO10 Cut Sheet



Hammond enclosure, NEMA 4/4X/12/13, 16 x 14 x 10in (HxWxD), wall mount, 5052-H32 aluminum, lift-off cover, aluminum clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1414N4ALO10>

Technical Specifications

Brand	Hammond
Item	Enclosure
Subpanel	Subpanel included
Slope Top	No
NEMA Rating	4/4X/12/13
IP Rating	IP66
Nominal Enclosure Dimensions	16 x 14 x 10in (HxWxD)
Enclosure Height	16.31in
Enclosure Width	14.31in
Enclosure Depth	10.21in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	5052-H32 aluminum
Cover Type	Lift-off cover
Latch Type	Aluminum clamps
Number Of Latches	10
Padlockable	No
Keylocking	No

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document