

1418N4D8 Cut Sheet



Hammond enclosure, NEMA 3R/4/12, 20 x 20 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, stainless steel clamps, padlock hasp and staple.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1418N4D8>

Technical Specifications

| | | | |
|-------------------------------------|-----------------------|----------------------------------|-------------------------|
| Brand | Hammond | Dual Access | No |
| Item | Enclosure | Knockouts | No |
| Subpanel | Subpanel included | Material | Carbon steel |
| Slope Top | No | Color | ANSI 61 gray |
| NEMA Rating | 3R/4/12 | Finish | Powder coat |
| IP Rating | IP66 | Cover Type | Single-door |
| Nominal Enclosure Dimensions | 20 x 20 x 8in (HxWxD) | Hinge Type | Continuous hinge |
| Enclosure Height | 20.00in | Number of Hinges Per Door | 1 |
| Enclosure Width | 20.00in | Latch Type | Stainless steel clamps |
| Enclosure Depth | 9.20in | Number Of Latches | 4 |
| Mounting | Wall | Padlock Attachment Type | Padlock hasp and staple |
| Integral Mounting Feet | Yes | Padlockable | Yes |
| Integral Mounting Flange | No | Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |