

1422B8F Cut Sheet



Hammond enclosure, NEMA 12, 60 x 48 x 8in (HxWxD), floor mount, carbon steel, ANSI 61 gray, powder coat finish, double-door, 3-point keylocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1422B8F>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Hammond |
| Item | Enclosure |
| Subpanel | Subpanel included |
| Slope Top | No |
| 3-Piece Assembly | No |
| Vented | No |
| NEMA Rating | 12 |
| IP Rating | IP54 |
| Nominal Enclosure Dimensions | 60 x 48 x 8in (HxWxD) |
| Enclosure Height | 60.13in |
| Enclosure Width | 48.06in |
| Enclosure Depth | 9.85in |
| Mounting | Floor |
| Integral Mounting Feet | No |
| Integral Mounting Flange | No |

| | |
|----------------------------------|---------------------------|
| Dual Access | No |
| Knockouts | No |
| Bottom Gland Plate | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Double-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | 3-point keylocking handle |
| Number Of Latches | 1 |
| Shelf | No |
| Padlockable | No |
| Keylocking | Yes |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1422B8F.pdf>
See store item page for other formats.