

1435MSSB Cut Sheet



Hammond pushbutton enclosure, 2 holes, 22mm, NEMA 3R/4/4X, 6 x 4 x 3in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1435MSSB>

Technical Specifications

| | |
|-------------------------------------|----------------------|
| Brand | Hammond |
| Item | Pushbutton enclosure |
| Number of Pushbutton Holes | 2 holes |
| Pushbutton Hole Nominal Size | 22mm |
| Slope Top | No |
| NEMA Rating | 3R/4/4X |
| IP Rating | IP66 |
| Nominal Enclosure Dimensions | 6 x 4 x 3in (HxWxD) |
| Enclosure Height | 6.06in |
| Enclosure Width | 3.56in |

| | |
|---------------------------------|---------------------|
| Enclosure Depth | 2.91in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |
| Dual Access | No |
| Knockouts | No |
| Material | 304 stainless steel |
| Finish | #4 brush |
| Cover Type | Screw cover |
| Padlockable | No |
| Keylocking | No |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1435MSSB.pdf>
See store item page for other formats.