

1435SSC Cut Sheet



Hammond pushbutton enclosure, 3 holes, 30mm, NEMA 3R/4/4X, 8 x 4 x 3in (HxWxD), wall mount, 304 stainless steel, #4 brush finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1435SSC>

Technical Specifications

Brand	Hammond
Item	Pushbutton enclosure
Number of Pushbutton Holes	3 holes
Pushbutton Hole Nominal Size	30mm
Slope Top	No
NEMA Rating	3R/4/4X
IP Rating	IP66
Nominal Enclosure Dimensions	8 x 4 x 3in (HxWxD)
Enclosure Height	8.31in
Enclosure Width	3.56in
Enclosure Depth	2.92in
Mounting	Wall
Integral Mounting Feet	Yes
Integral Mounting Flange	No
Dual Access	No
Knockouts	No
Material	304 stainless steel
Finish	#4 brush
Cover Type	Screw cover

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	LR21001
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document