

1447SB8HK Cut Sheet



Hammond disconnect enclosure, NEMA 4/12/13, right flange, 24 x 21 x 8in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, 2-point padlocking handle.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SB8HK>

Technical Specifications

| | |
|-------------------------------------|-----------------------|
| Brand | Hammond |
| Item | Disconnect enclosure |
| Slope Top | No |
| NEMA Rating | 4/12/13 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 24 x 21 x 8in (HxWxD) |
| Enclosure Height | 24.00in |
| Enclosure Width | 21.38in |
| Enclosure Depth | 8.88in |
| Mounting | Wall |
| Integral Mounting Feet | Yes |
| Integral Mounting Flange | No |
| Dual Access | No |

| | |
|----------------------------------|---|
| Knockouts | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | 2-point padlocking handle |
| Padlockable | Yes |
| Keylocking | No |
| Subpanel | Subpanel included |
| Additional Information | Purchase operating mechanism, disconnect switch or circuit breaker, and operating handle from disconnect supplier |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |