

1447SN4L12 Cut Sheet



Hammond disconnect enclosure, NEMA 3R/4/12, right flange, 60 x 37 x 12in (HxWxD), wall mount, carbon steel, ANSI 61 gray, powder coat finish, single-door, stainless steel clamps.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1447SN4L12>

Technical Specifications

| | |
|-------------------------------------|------------------------|
| Brand | Hammond |
| Item | Disconnect enclosure |
| Slope Top | No |
| Vented | No |
| NEMA Rating | 3R/4/12 |
| IP Rating | IP66 |
| Disconnect Mounting | Right flange |
| Nominal Enclosure Dimensions | 60 x 37 x 12in (HxWxD) |
| Enclosure Height | 60.00in |
| Enclosure Width | 37.38in |
| Enclosure Depth | 13.19in |
| Mounting | Wall |

| | |
|----------------------------------|------------------------|
| Integral Mounting Feet | Yes |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Single-door |
| Hinge Type | Continuous hinge |
| Number of Hinges Per Door | 1 |
| Latch Type | Stainless steel clamps |
| Padlockable | No |
| Keylocking | No |
| Subpanel | Subpanel included |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1447SN4L12.pdf>
See store item page for other formats.