

1481SDH3024 Cut Sheet



Hammond universal deep-hinged door, NEMA 4/12, 28.19 x 20.14 x 2.75in, carbon steel, ANSI 61 gray, concealed hinges. For use with wall-mount enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481SDH3024>

Technical Specifications

Brand	Hammond
Item	Universal deep-hinged door
NEMA Rating	4/12
Door Size	28.19 x 20.14 x 2.75in
Door Material	Carbon steel
Hinge Type	Concealed hinges
Color	ANSI 61 gray
Finish	Powder coat
Cutout Size	25.19 x 17.14in
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush oil-tight latch
Gasket Type	Oil-resistant neoprene
For Use With	Wall-mount enclosures

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement