

1481SSDH1620 Cut Sheet



Hammond universal deep-hinged door, NEMA 4/4X/12, 14.19 x 16.14 x 2.75in, 316L stainless steel, concealed hinges. For use with wall-mount enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481SSDH1620>

Technical Specifications

Brand	Hammond
Item	Universal deep-hinged door
NEMA Rating	4/4X/12
Door Size	14.19 x 16.14 x 2.75in
Door Material	316L stainless steel
Hinge Type	Concealed hinges
Finish	#4 brush
Cutout Size	11.19 x 13.14in
Number of Hinges Per Door	2
Latch Type	1/4-turn semi-flush oil-tight latch
Gasket Type	Oil-resistant neoprene
For Use With	Wall-mount enclosures

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1481SSDH1620.pdf>
See store item page for other formats.