

1481WN42919 Cut Sheet



Hammond enclosure window, 29.00 x 19.00in window, UV-resistant polycarbonate, 31.63 x 21.63in frame, carbon steel, ANSI 61 gray, powder coat finish, oil-resistant neoprene gasket. For use with NEMA 4 enclosures. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481WN42919>

Technical Specifications

Brand	Hammond
Item	Enclosure window
Window Size	29.00 x 19.00in
Window Material	UV-resistant polycarbonate
Frame Size	31.63 x 21.63in
Frame Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat
Gasket Type	Oil-resistant neoprene
Cutout Size	30.69 x 20.69in
For Use With	NEMA 4 enclosures
Includes	Mounting hardware

Agency Approvals

UL Listed File #	E65324
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1481WN42919.pdf>
See store item page for other formats.