

1481WSSDH3624 Cut Sheet



Hammond universal deep-hinged door, NEMA 4/4X/12, 34.19 x 20.14 x 2.75in, 316L stainless steel, concealed hinges, polycarbonate window. For use with wall-mount enclosures.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1481WSSDH3624>

Technical Specifications

| | |
|----------------------|----------------------------|
| Brand | Hammond |
| Item | Universal deep-hinged door |
| NEMA Rating | 4/4X/12 |
| Door Size | 34.19 x 20.14 x 2.75in |
| Door Material | 316L stainless steel |
| Hinge Type | Concealed hinges |
| Finish | #4 brush |
| Cutout Size | 31.19 x 17.14in |

| | |
|----------------------------------|-------------------------------------|
| Number of Hinges Per Door | 2 |
| Latch Type | 1/4-turn semi-flush oil-tight latch |
| Gasket Type | Oil-resistant neoprene |
| Window Material | Polycarbonate |
| Window Size | 30.00 x 14.75in |
| For Use With | Wall-mount enclosures |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LL21312 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1481WSSDH3624.pdf>
See store item page for other formats.