

1485C24 Cut Sheet



Hammond 1485 series lay-in wireway, 4 x 4 x 24in, carbon steel, ANSI 61 gray, powder coat finish, hinged cover, quick-release clamps, NEMA 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1485C24>

Technical Specifications

Brand	Hammond
Item	Wireway
Series	1485
Wireway Type	Lay-in
Size	4 x 4 x 24in
Material	Carbon steel
Color	ANSI 61 gray
Finish	Powder coat

Cover Type	Hinged cover
Latch Type	Quick-release clamps
Knockouts	No
NEMA Rating	12
IP Rating	IP54
Includes	(1) snap-on flat sealing plate and (1) gasket kit complete with hardware

Agency Approvals

UL Listed File #	E186830
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	LL21312
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1485C24.pdf>
See store item page for other formats.