

1485C36 Cut Sheet

Hammond 1485 series lay-in wireway, 4 x 4 x 36in, carbon steel, ANSI 61 gray, powder coat finish, quick-release clamps, NEMA 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1485C36>

Technical Specifications

| | |
|---------------------|--------------|
| Brand | Hammond |
| Item | Wireway |
| Wireway Type | Lay-in |
| Size | 4 x 4 x 36in |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |

| | |
|--------------------|--|
| Cover Type | Hinged |
| Latch Type | Quick-release clamps |
| Knockouts | No |
| NEMA Rating | 12 |
| IP Rating | IP54 |
| Includes | (1) snap-on flat sealing plate and (1) gasket kit complete with hardware |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | E186830 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CSA File # | LL21312 |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1485C36.pdf>
See store item page for other formats.