

# 1485E36 Cut Sheet



Hammond 1485 series lay-in wireway, 8 x 8 x 36in, carbon steel, ANSI 61 gray, powder coat finish, quick-release clamps, NEMA 12.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1485E36>

## Technical Specifications

|                     |              |
|---------------------|--------------|
| <b>Brand</b>        | Hammond      |
| <b>Item</b>         | Wireway      |
| <b>Wireway Type</b> | Lay-in       |
| <b>Size</b>         | 8 x 8 x 36in |
| <b>Material</b>     | Carbon steel |
| <b>Color</b>        | ANSI 61 gray |
| <b>Finish</b>       | Powder coat  |

|                    |  |
|--------------------|--|
| <b>Cover Type</b>  | Hinged   |
| <b>Latch Type</b>  | Quick-release clamps   |
| <b>Knockouts</b>   | No   |
| <b>NEMA Rating</b> | 12   |
| <b>IP Rating</b>   | IP54   |
| <b>Includes</b>    | (1) snap-on flat sealing plate and (1) gasket kit complete with hardware |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E186830   |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | LL21312   |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1485E36.pdf>  
See store item page for other formats.