

# 1486B30 Cut Sheet

Hammond wiring trough, 2.5 x 2.5 x 30in (HxDxL), NEMA 1/4/12, carbon steel, ANSI 61 gray, powder coat finish, single-door.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1486B30>

## Technical Specifications

|                                     |                      |
|-------------------------------------|----------------------|
| <b>Brand</b>                        | Hammond              |
| <b>Item</b>                         | Wiring trough        |
| <b>NEMA Rating</b>                  | 1/4/12               |
| <b>IP Rating</b>                    | IP54                 |
| <b>Nominal Enclosure Dimensions</b> | 3 x 30 x 3in (HxWxD) |
| <b>Enclosure Height</b>             | 2.88in               |
| <b>Enclosure Depth</b>              | 2.67in               |
| <b>Enclosure Length</b>             | 30.38in              |
| <b>Knockouts</b>                    | No                   |
| <b>Material</b>                     | Carbon steel         |
| <b>Color</b>                        | ANSI 61 gray         |
| <b>Finish</b>                       | Powder coat          |
| <b>Cover Type</b>                   | Single-door          |
| <b>Latch Type</b>                   | Screw clamps         |
| <b>Padlockable</b>                  | No                   |

## Agency Approvals

|                             |   |
|-----------------------------|---|
| <b>UL Listed File #</b>     | E186830   |
| <b>UL Recognized File #</b> | None  |
| <b>UL Hazardous File #</b>  | None  |
| <b>CSA File #</b>           | LR21312   |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |