

# 1488HL9 Cut Sheet



Hammond operator console, NEMA 12/13, 11 x 20 x 9in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish, screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1488HL9>

## Technical Specifications

|                                     |                       |
|-------------------------------------|-----------------------|
| <b>Brand</b>                        | Hammond               |
| <b>Item</b>                         | Operator console      |
| <b>Slope Top</b>                    | No                    |
| <b>3-Piece Assembly</b>             | No                    |
| <b>Vented</b>                       | No                    |
| <b>NEMA Rating</b>                  | 12/13                 |
| <b>IP Rating</b>                    | IP54                  |
| <b>Nominal Enclosure Dimensions</b> | 11 x 20 x 9in (HxWxD) |
| <b>Enclosure Height</b>             | 11.51in               |
| <b>Enclosure Width</b>              | 20.34in               |
| <b>Enclosure Depth</b>              | 9.37in                |
| <b>Mounting</b>                     | Desktop or pedestal   |
| <b>Integral Mounting Feet</b>       | No                    |
| <b>Integral Mounting Flange</b>     | No                    |

|                               |                                     |
|-------------------------------|-------------------------------------|
| <b>Dual Access</b>            | No                                  |
| <b>Knockouts</b>              | No                                  |
| <b>Bottom Gland Plate</b>     | No                                  |
| <b>Material</b>               | Carbon steel                        |
| <b>Color</b>                  | ANSI 61 gray                        |
| <b>Finish</b>                 | Powder coat                         |
| <b>Cover Type</b>             | Screw cover                         |
| <b>Hinge Type</b>             | Continuous hinge                    |
| <b>Number of Lid Hinges</b>   | 1                                   |
| <b>Shelf</b>                  | No                                  |
| <b>Padlockable</b>            | No                                  |
| <b>Keylocking</b>             | No                                  |
| <b>Additional Information</b> | Purchase pedestal column separately |

## Agency Approvals

|                             |  |
|-----------------------------|--|
| <b>UL Listed File #</b>     | E65324                                 |
| <b>UL Recognized File #</b> | None                                   |
| <b>UL Hazardous File #</b>  | None                                   |
| <b>CE</b>                   | <a href="#">View CE declarations</a>   |
| <b>CSA File #</b>           | LR21001                                |
| <b>RoHS Status</b>          | Yes (See CE Doc)                       |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a> |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1488HL9.pdf>  
See store item page for other formats.