

1490MG4 Cut Sheet



Hammond pushbutton console, 4 holes, 22mm, NEMA 12/13, 7 x 7 x 7in (HxWxD), desktop or pedestal mount, carbon steel, ANSI 61 gray, powder coat finish, hinged screw cover.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1490MG4>

Technical Specifications

| | |
|-------------------------------------|---------------------|
| Brand | Hammond |
| Item | Pushbutton console |
| Slope Top | No |
| NEMA Rating | 12/13 |
| IP Rating | IP54 |
| Nominal Enclosure Height | 7in |
| Nominal Enclosure Width | 7in |
| Nominal Enclosure Depth | 7in |
| Mounting | Desktop or pedestal |
| Number of Pushbutton Holes | 4 holes |
| Pushbutton Hole Nominal Size | 22mm |

| | |
|----------------------------------|--|
| Integral Mounting Flange | Yes |
| Dual Access | No |
| Material | Carbon steel |
| Color | ANSI 61 gray |
| Finish | Powder coat |
| Cover Type | Hinged screw cover |
| Hinge Type | Internal lift-off hinge |
| Number of Hinges Per Door | 2 |
| Padlockable | No |
| Keylocking | No |
| Additional Information | Purchase optional pedestal column separately |

Agency Approvals

| | |
|-----------------------------|--|
| UL Listed File # | E65324 |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | View CE declarations |
| CSA File # | LR21001 |
| RoHS Status | Yes (See CE Doc) |
| EU REACH | View EU REACH document |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1490MG4.pdf>
See store item page for other formats.