

# 1501-1466 Cut Sheet



ASO Safety Solutions safety contact edge, 15 x 10mm, 1.8ft length, pigtail, 8.2ft/2.5m cable length. Aluminum mounting rail included. Preassembled with 8.2k ohm resistor for 2-wire installation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1501-1466>

## Technical Specifications

<b>Brand</b>	ASO Safety Solutions
<b>Item</b>	Safety contact edge
<b>Size</b>	15 x 10mm
<b>Length</b>	1.8ft
<b>Actuation Force</b>	42.9N
<b>Switching Cycles</b>	>10,000 cycles
<b>Operating Voltage</b>	24 VAC/VDC
<b>Contact Surface Material</b>	TPE
<b>Operating Temperature</b>	0 to 50 deg C
<b>Connection</b>	Pigtail
<b>Cable Length</b>	8.2ft/2.5m
<b>Conductor Size</b>	22 AWG
<b>Includes</b>	Aluminum mounting rail
<b>Additional Information</b>	Preassembled with 8.2k ohm resistor for 2-wire installation

## Agency Approvals

<b>UL Recognized File #</b>	E341185
<b>CE</b>	<a href="#">View CE declarations</a>
<b>RoHS Status</b>	Yes (See CE Doc)
<b>EU REACH</b>	<a href="#">View EU REACH document</a>

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1501-1466.pdf>  
See store item page for other formats.