

1501-1467 Cut Sheet



ASO Safety Solutions safety contact edge, 15 x 10mm, 2ft length, pigtail, 8.2ft/2.5m cable length. Aluminum mounting rail included. Preassembled with 8.2k ohm resistor for 2-wire installation.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1501-1467>

Technical Specifications

Brand	ASO Safety Solutions
Item	Safety contact edge
Size	15 x 10mm
Length	2ft
Actuation Force	42.9N
Switching Cycles	>10,000 cycles
Operating Voltage	24 VAC/VDC
Contact Surface Material	TPE
Operating Temperature	0 to 50 deg C
Connection	Pigtail
Cable Length	8.2ft/2.5m
Conductor Size	22 AWG
Includes	Aluminum mounting rail
Additional Information	Preassembled with 8.2k ohm resistor for 2-wire installation

Agency Approvals

UL Recognized File #	E341185
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1501-1467.pdf>
See store item page for other formats.