

151137 Cut Sheet



FATH swivel caster, silver/gray, thermoplastic polyurethane/nylon/steel. For use with all 1.5in, 3in, 40mm, 45mm, 80mm and 90mm profile T-slotted rails. Double brake and mounting plate included. Manufacturer part number: 098S100UD4045N.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/151137>

Technical Specifications

Brand	FATH
Item	Swivel caster
Series	15 Series, 40 Series and 45 Series
Color	Silver/gray
Material	Thermoplastic polyurethane/nylon/steel
Load Rating	269 lb/122 kg
For Use With	All 1.5in, 3in, 40mm, 45mm, 80mm and 90mm profile T-slotted rails
Includes	Double brake and mounting plate
Manufacturer Part Number	098S100UD4045N

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement