

# 1555J2F42GY Cut Sheet



Hammond enclosure, NEMA 4/4X/6/6P/12/13, 160 x 91 x 63mm (HxWxD), integral mounting flange, polycarbonate, RAL 7035 light gray, screw cover, purchase subpanel separately.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1555J2F42GY>

## Technical Specifications

|                                 |                              |
|---------------------------------|------------------------------|
| <b>Brand</b>                    | Hammond                      |
| <b>Item</b>                     | Enclosure                    |
| <b>Subpanel</b>                 | Purchase subpanel separately |
| <b>NEMA Rating</b>              | 4/4X/6/6P/12/13              |
| <b>IP Rating</b>                | IP68                         |
| <b>Enclosure Height</b>         | 160.00mm                     |
| <b>Enclosure Width</b>          | 91.00mm                      |
| <b>Enclosure Depth</b>          | 63.00mm                      |
| <b>Cover Type</b>               | Screw cover                  |
| <b>Cover Depth</b>              | 47mm                         |
| <b>Integral Mounting Flange</b> | Yes                          |
| <b>Material</b>                 | Polycarbonate                |
| <b>Color</b>                    | RAL 7035 light gray          |

## Agency Approvals

|                             |                                                                     |
|-----------------------------|---------------------------------------------------------------------|
| <b>UL Listed File #</b>     | E65324                                                              |
| <b>UL Recognized File #</b> | None                                                                |
| <b>UL Hazardous File #</b>  | None                                                                |
| <b>CSA File #</b>           | None                                                                |
| <b>RoHS Status</b>          | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| <b>EU REACH</b>             | <a href="#">View EU REACH document</a>                              |
| <b>Other</b>                | <a href="#">RoHS Statement</a>                                      |

## Dimensional Drawings



2D Drawing PDF Link:  
<https://cdn.automationdirect.com/static/drawings/1555J2F42GY.pdf>  
See store item page for other formats.