

1602-4560 Cut Sheet



ASO Safety Solutions safety contact mat, 24 x 24in, integrated taper edge, 24 VAC/VDC operating voltage, polyurethane contact surface, black, IP65, 19.6ft/6m cable length, pigtail.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/1602-4560>

Technical Specifications

Brand	ASO Safety Solutions
Item	Safety contact mat
Size	24 x 24in
Actuation Force	150N
Response Time	< 25ms
Switching Cycles	> 1,000,000 cycles
Static Load	2000N
Edge	Integrated taper
Operating Voltage	24 VAC/VDC
Contact Surface Material	Polyurethane
Color	Black
IP Rating	IP65
Operating Temperature	-10 to 55C
Cable Length	19.6ft/6m
Connection	Pigtail
Conductor Size	22 AWG

Agency Approvals

UL Listed File #	E329422
CE	View CE declarations
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/1602-4560.pdf>
See store item page for other formats.