

16170070 Cut Sheet



WERMA EvoSIGNAL Midi series audible signal horn, 110 dB at 1m, 3.3 kHz tone frequency, (10) selectable tone(s), 12/24 VAC/VDC, modular mount, ABS/polycarbonate housing, gray, IP66. Requires mounting adapter.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/16170070>

Technical Specifications

Brand	WERMA
Item	Audible signal horn
Series	EvoSIGNAL Midi
Loudness Decibel	110 dB at 1m
Tone Frequency	3.3 kHz
Tone Type	(10) selectable
Touch to Acknowledge	No
Number of Alarms	10
Voltage Rating	12/24 VAC/VDC
Mounting	Modular
Housing Material	ABS/polycarbonate
Color	Gray
IP Rating	IP66
Requires	Mounting adapter

Agency Approvals

UL Listed File #	E164155
UL Recognized File #	None
UL Hazardous File #	None
CE	View CE declarations
CSA File #	None
RoHS Status	Yes (See CE Doc)
EU REACH	View EU REACH document

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/16170070.pdf>
See store item page for other formats.