

163010 Cut Sheet



FATH leveling caster, off-white, M12-1.75, die-cast aluminum/steel/nylon/rubber, slot size 6/8/10. For use with all 1.5in, 2in, 3in, 60mm, 80mm and 90mm profile T-slotted rails. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/163010>

Technical Specifications

| | |
|--------------------|--|
| Brand | FATH |
| Item | Leveling caster |
| Series | 10 Series, 15 Series, 30 Series, 40 Series and 45 Series |
| Color | Off-white |
| Thread Size | M12-1.75 |
| Material | Die-cast aluminum/steel/nylon/rubber |

| | |
|---------------------------------|--|
| Slot Size | 6/8/10 |
| Load Rating | 551 lb/250 kg |
| For Use With | All 1.5in, 2in, 3in, 60mm, 80mm and 90mm profile T-slotted rails |
| Includes | Mounting hardware |
| Requires | FATH transport/base plate with M12-1.75 threads |
| Manufacturer Part Number | 098LF050AF46 |

Agency Approvals

| | |
|-----------------------------|---|
| UL Listed File # | None |
| UL Recognized File # | None |
| UL Hazardous File # | None |
| CE | None |
| CSA File # | None |
| RoHS Status | Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below) |
| EU REACH | View EU REACH document |
| Other | RoHS Statement |

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/163010.pdf>
See store item page for other formats.