

172518 Cut Sheet



FATH 4-axis dual monitor workstation, silver, 936 x 800 x 488mm, die-cast aluminum/plastic/steel, slot size 8/10. For use with all 1.5in, 3in, 40mm, 45mm, 80mm and 90mm profile T-slotted rails. Mounting hardware included.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/172518>

Technical Specifications

Brand	FATH
Item	4-axis dual monitor workstation
Series	15 Series, 40 Series and 45 Series
Color	Silver
Size	936 x 800 x 488mm
Material	Die-cast aluminum/plastic/steel
Slot Size	8/10
For Use With	All 1.5in, 3in, 40mm, 45mm, 80mm and 90mm profile T-slotted rails
Includes	Mounting hardware
Manufacturer Part Number	6MHM75100S40ITD

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CE	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement

Dimensional Drawings



2D Drawing PDF Link:
<https://cdn.automationdirect.com/static/drawings/2d/172518.pdf>
See store item page for other formats.