


2000-5420-1399-0987 Cut Sheet



WAGO PNP/NPN converter, 19.2-28.8 VDC input, 24 VDC output, 0.1A, 2.4W, plastic housing, 35mm DIN rail mount, cage clamp.

For complete product information, please see this item on our store at the following link:



<https://www.automationdirect.com/pn/2000-5420-1399-0987>

Technical Specifications

Brand	WAGO
Item	PNP/NPN converter
Input voltage range	19.2-28.8 VDC
Output Voltage Range	24 VDC
Load Current	0.1A
Output Power	2.4W
Housing Material	Plastic
Encapsulated	No
Mounting	35mm DIN rail
Terminal Block Type	Cage clamp
Removable	No
Number of Isolated Commons	1

Agency Approvals

UL Listed File #	None
UL Recognized File #	None
UL Hazardous File #	None
CSA File #	None
RoHS Status	Meets RoHS Chemical Restrictions - No CE (See RoHS Statement Below)
EU REACH	View EU REACH document
Other	RoHS Statement